

**F4A-PKRDM-2M****FSJ4-50B SureFlex® Jumper with interface types 4.1-9.5 DIN Male Right Angle and 7-16 DIN Male, 2 m**

General Specifications

Body Style, Connector A	Right angle
Body Style, Connector B	Straight
Cable Family	FSJ4-50B
Interface, Connector A	4.1-9.5 DIN Male
Interface, Connector B	7-16 DIN Male
Nominal Size	1/2 in
Length	2.000 m 6.562 ft
Specification Sheet Revision Level	A

Electrical Specifications

DTF, Connector A	-32.00 dB
DTF, Connector B	-32.00 dB

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR, typical	Return Loss, typical (dB)
0-3000 MHz	1.11	26.00
2.2-2.7 GHz	1.08	28.00

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Product Specifications

COMMScope®

F4A-PKRD-M-2M

POWERED BY



Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket