

F4A-PNFDF

FSJ4-50B SureFlex™ Jumper with interface types N Female and 7-16 DIN Female, variable length

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FSJ4-50B
Interface, Connector A	N Female
Interface, Connector B	7-16 DIN Female
Variable Length	For custom lengths contact 1-800-255-1479 (North America), 1-779-435-6500 (International), or an Andrew representative

Electrical Specifications

DTF, Connector A	-32.00 dB
DTF, Connector B	-32.00 dB

Jumper Assembly Sample Label



Regulatory Compliance/Certifications


Agency	Classification
RoHS 2002/95/EC	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

Product Specifications



F4A-PNDFD

L4DR-PS — 7-16 DIN Male Right Angle Positive Stop™ for 1/2 in LDF4-50A cable

L4NR-PS — Type N Male Right Angle Positive Stop™ for 1/2 in LDF4-50A cable

F4DR-C — 7-16 DIN Male Right Angle for 1/2 in FSJ4-50B cable

F4NR-HC — Type N Male Right Angle for 1/2 in FSJ4-50B cable