



F4A-PNMDM-4M

FSJ4-50B SureFlex® Jumper with interface types N Male and 7-16 DIN Male, 4 m

General Specifications

| | |
|------------------------------------|---------------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Cable Family | FSJ4-50B |
| Interface, Connector A | N Male |
| Interface, Connector B | 7-16 DIN Male |
| Nominal Size | 1/2 in |
| Length | 4.000 m 13.123 ft |
| Specification Sheet Revision Level | A |

Electrical Specifications

| | |
|------------------|-----------|
| DTF, Connector A | -32.00 dB |
| DTF, Connector B | -32.00 dB |

Jumper Assembly Sample Label



Return Loss/VSWR

| Frequency Band | VSWR, typical | Return Loss, typical (dB) |
|----------------|---------------|---------------------------|
| 0-3000 MHz | 1.11 | 26.00 |
| 2.2-2.7 GHz | 1.08 | 28.00 |

Regulatory Compliance/Certifications

| Agency | Classification |
|----------------------------|--|
| RoHS 2011/65/EU | Compliant by Exemption |
| China RoHS SJ/T 11364-2006 | Above Maximum Concentration Value (MCV) |
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |

Product Specifications

COMMScope®

F4A-PNMDM-4M



Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket