

**F4A-PNMNM-12-MA****FSJ4-50B SureFlex® Jumper with interface types N Male and N Male, 3.658 m****OBSOLETE****This product was discontinued on: January 2, 2014**

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FSJ4-50B
Interface, Connector A	N Male
Interface, Connector B	N Male
Nominal Size	1/2 in
Length	3.658 m 12.001 ft
Specification Sheet Revision Level	A

Electrical Specifications

DTF, Connector A	-32.00 dB
DTF, Connector B	-32.00 dB

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)	VSWR, typical	Return Loss, typical (dB)
0-3000 MHz			1.11	26.00
2.2-2.7 GHz			1.08	28.00
2300-2500 MHz	1.35	16.60		

F4A-PNMMN-12-MA

POWERED BY



Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

China RoHS SJ/T 11364-2006

ISO 9001:2008

Classification

Compliant by Exemption

Above Maximum Concentration Value (MCV)

Designed, manufactured and/or distributed under this quality management system



Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket