



## F4A-PNMNM-8-MA

**FSJ4-50B SureFlex™ Jumper with interface types N Male and N Male, 2.438 m**

### General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FSJ4-50B
Interface, Connector A	N Male
Interface, Connector B	N Male
Length	2.438 m   7.999 ft

### Electrical Specifications

DTF, Connector A	-32.00 dB
DTF, Connector B	-32.00 dB

### Jumper Assembly Sample Label



### Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



### Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket