



F4A-PNR

**FSJ4-50B SureFlex® Jumper with interface type N Male Right Angle, variable length**



## General Specifications

|                                    |  |
|------------------------------------|--|
| Body Style, Connector A            | Right angle  |
| Cable Family                       | FSJ4-50B   |
| Interface, Connector A             | N Male   |
| Interface, Connector B             | Sold separately  |
| Nominal Size                       | 1/2 in   |
| Specification Sheet Revision Level | A  |
| Variable Length                    | For custom lengths contact 1-800-255-1479 (North America), 1-779-435-6500 (International), or an Andrew representative |

## Electrical Specifications

|                  |           |
|------------------|-----------|
| DTF, Connector A | -32.00 dB |
|------------------|-----------|

## Jumper Assembly Sample Label



## Return Loss/VSWR

| Frequency Band | VSWR, typical | Return Loss, typical (dB) |
|----------------|---------------|---------------------------|
| 0-3000 MHz     | 1.11          | 26.00                     |
| 2.2-2.7 GHz    | 1.08          | 28.00                     |

## Regulatory Compliance/Certifications

| Agency                     | Classification   |
|----------------------------|--|
| RoHS 2011/65/EU            | Compliant by Exemption   |
| China RoHS SJ/T 11364-2006 | Above Maximum Concentration Value (MCV)  |
| ISO 9001:2008              | Designed, manufactured and/or distributed under this quality management system |

F4A-PNR



## Included Products

---

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket