



F4A-PNRDM-8M-X

**FSJ4-50B SureFlex® Jumper with interface types N Male Right Angle and 7-16 DIN Male, 8 m**

## General Specifications

Body Style, Connector A	Right angle
Body Style, Connector B	Straight
Cable Family	FSJ4-50B
Interface, Connector A	N Male
Interface, Connector B	7-16 DIN Male
Nominal Size	1/2 in
Length	8.000 m   26.247 ft
Attachment, Connector B	Field attachment
Specification Sheet Revision Level	A

## Electrical Specifications

DTF, Connector A	-32.00 dB
------------------	-----------

## Jumper Assembly Sample Label



## Return Loss/VSWR

Frequency Band	VSWR, typical	Return Loss, typical (dB)
0-3000 MHz	1.11	26.00
2.2-2.7 GHz	1.08	28.00

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)

# Product Specifications

COMMSCOPE®

F4A-PNRDM-8M-X



ISO 9001:2008

Designed, manufactured and/or distributed under this quality management system



## Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

F4PDMV2-C — 7-16 DIN Male for 1/2 in FSJ4-50B cable