

**F4A-PNRNR****FSJ4-50B SureFlex™ Jumper with interface types N Male Right Angle and N Male Right Angle, variable length**

## General Specifications

Body Style, Connector A Right angle

Body Style, Connector B Right angle

Cable Family FSJ4-50B

Interface, Connector A N Male

Interface, Connector B N Male

Variable Length For custom lengths contact 1-800-255-1479 (North America), 1-779-435-6500 (International), or an Andrew representative

## Electrical Specifications

DTF, Connector A -32.00 dB

DTF, Connector B -32.00 dB

## Jumper Assembly Sample Label



## Return Loss/VSWR

Frequency Band	VSWR, typical	Return Loss, typical (dB)
0-3000 MHz	1.11	26.00
2.2-2.7 GHz	1.08	28.00

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

F4A-PNRNR



POWERED BY



## Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

F4PNR-HA — Type N Male Right Angle for 1/2 in FSJ4-50B cable, factory attached