



## F4A-XNMNM-2M

**FSJ4-50B SureFlex™ Jumper with interface types N Male and N Male, 2 m**

### General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FSJ4-50B
Interface, Connector A	N Male
Interface, Connector B	N Male
Length	2.000 m   6.562 ft

### Electrical Specifications

3rd Order IMD	-116.00 dBm
DTF, Connector A	-32.00 dB
DTF, Connector B	-32.00 dB

### Jumper Assembly Sample Label



### Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
806–960 MHz	1.05	32.00
1700–2170 MHz	1.06	30.00

### Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



### Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket