



F4B-PNFNR-3.5-DDH

FSJ4-50B SureFlex® Jumper with interface types N Female Bulkhead and N Male Right Angle, 1.07 m

General Specifications

Body Style, Connector A	Bulkhead
Body Style, Connector B	Right angle
Cable Family	FSJ4-50B
Interface, Connector A	N Female
Interface, Connector B	N Male
Nominal Size	1/2 in
Length	1.070 m 3.510 ft
Orientation	0°
Specification Sheet Revision Level	A

Electrical Specifications

DTF, Connector A	-32.00 dB
DTF, Connector B	-32.00 dB

Jumper Assembly Sample Label



Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Product Specifications

COMMSCOPE®

F4B-PNFNR-3.5-DDH



Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

F4PNF-BH — Type N Female Bulkhead for 1/2 in cable