

**F4B-PNFNr-6.17-DDH****FSJ4-50B SureFlex® Jumper with interface types N Female Bulkhead and N Male Right Angle, 1.88 m**

## General Specifications

|                                    |                    |
|------------------------------------|--------------------|
| Body Style, Connector A            | Bulkhead           |
| Body Style, Connector B            | Right angle        |
| Cable Family                       | FSJ4-50B           |
| Interface, Connector A             | N Female           |
| Interface, Connector B             | N Male             |
| Nominal Size                       | 1/2 in             |
| Length                             | 1.880 m   6.168 ft |
| Orientation                        | 0°                 |
| Specification Sheet Revision Level | A                  |

## Electrical Specifications

|                  |           |
|------------------|-----------|
| DTF, Connector A | -32.00 dB |
| DTF, Connector B | -32.00 dB |

## Jumper Assembly Sample Label



## Regulatory Compliance/Certifications

| Agency                     | Classification   |
|----------------------------|--|
| RoHS 2011/65/EU            | Compliant by Exemption   |
| China RoHS SJ/T 11364-2006 | Above Maximum Concentration Value (MCV)  |
| ISO 9001:2008              | Designed, manufactured and/or distributed under this quality management system |

F4B-PNFR-6.17-DDH



POWERED BY



## Included Products

FSJ4-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

F4PNF-BH — Type N Female Bulkhead for 1/2 in cable