



F4RNA-PDMDM-7M

FSJ4RK-50B SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 7 m

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FSJ4-50B
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Male
Nominal Size	1/2 in
Length	7.000 m 22.966 ft
Specification Sheet Revision Level	A

Electrical Specifications

DTF, Connector A	-32.00 dB
DTF, Connector B	-32.00 dB

Jumper Assembly Sample Label



Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Product Specifications

COMMSCOPE®

F4RNA-PDMDM-7M



Included Products

FSJ4RK-50B — FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black non-halogenated, fire retardant polyolefin jacket