



F4RNA-PDRNM-10M-X

FSJ4RK-50B SureFlex® Jumper with interface types 7-16 DIN Male Right Angle and N Male, 10 m

General Specifications

Body Style, Connector A	Right angle
Body Style, Connector B	Straight
Cable Family	FSJ4-50B
Interface, Connector A	7-16 DIN Male
Interface, Connector B	N Male
Nominal Size	1/2 in
Length	10.000 m 32.808 ft
Attachment, Connector B	Field attachment
Specification Sheet Revision Level	A

Electrical Specifications

DTF, Connector A	-32.00 dB
------------------	-----------

Jumper Assembly Sample Label

Batch: 0123456789 | Manufacturing Date (two digit year and week): US22 1240 | Product Revision: /A

COMMSCOPE® Andrew Solutions™
F4A-DMDM-2M-P — Part Number
2 M (6.562 FT)
SUREFLEX ASSEMBLY
U.S. PATENT 5802710
Product of UNITED STATES | 12US220001242 — Serial Number

Barcode: 12US220001242

Regulatory Compliance/Certifications

Agency RoHS 2011/65/EU China RoHS SJ/T 11364-2006 ISO 9001:2008	Classification Compliant by Exemption Above Maximum Concentration Value (MCV) Designed, manufactured and/or distributed under this quality management system
---	--



Product Specifications

COMMSCOPE®

F4RNA-PDRNM-10M-X



Included Products

F4PNMV2-HC — Type N Male for 1/2 in FSJ4-50B cable