

POWERED BY

**F4RNA-PNM-3M****FSJ4RK-50B SureFlex® Jumper with interface type N Male, 3 m**

General Specifications

| | |
|------------------------------------|--------------------|
| Body Style, Connector A | Straight |
| Cable Family | FSJ4-50B |
| Interface, Connector A | N Male |
| Interface, Connector B | Sold separately |
| Nominal Size | 1/2 in |
| Length | 3.000 m 9.843 ft |
| Specification Sheet Revision Level | A |

Electrical Specifications

| | |
|------------------|-----------|
| DTF, Connector A | -32.00 dB |
|------------------|-----------|

Jumper Assembly Sample Label



Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
China RoHS SJ/T 11364-2006
ISO 9001:2008

Classification

Compliant by Exemption
Above Maximum Concentration Value (MCV)
Designed, manufactured and/or distributed under this quality management system

