



F4RNA-PNMDM-M5

FSJ4RK-50B SureFlex® Jumper with interface types N Male and 7-16 DIN Male, 0.5 m

General Specifications

| | |
|------------------------------------|--------------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Cable Family | FSJ4-50B |
| Interface, Connector A | 7-16 DIN Male |
| Interface, Connector B | 7-16 DIN Male |
| Nominal Size | 1/2 in |
| Length | 0.500 m 1.640 ft |
| Specification Sheet Revision Level | A |

Electrical Specifications

| | |
|------------------|-----------|
| DTF, Connector A | -32.00 dB |
| DTF, Connector B | -32.00 dB |

Jumper Assembly Sample Label



Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
China RoHS SJ/T 11364-2006
ISO 9001:2008

Classification

Compliant by Exemption
Above Maximum Concentration Value (MCV)
Designed, manufactured and/or distributed under this quality management system

