



F4RNA-PNRDF-1M5

FSJ4RK-50B SureFlex® Jumper with interface types N Male Right Angle and 7-16 DIN Female, 1.5 m

General Specifications

Body Style, Connector A	Right angle
Body Style, Connector B	Straight
Cable Family	FSJ4-50B
Interface, Connector A	N Male
Interface, Connector B	7-16 DIN Female
Nominal Size	1/2 in
Length	1.500 m 4.921 ft
Specification Sheet Revision Level	A

Electrical Specifications

DTF, Connector A	-32.00 dB
DTF, Connector B	-32.00 dB

Jumper Assembly Sample Label

0123456789 US22 1240 /A

COMMScope® Andrew Solutions™

F4A-DMDM-2M-P — Part Number

2 M (6.562 FT)

SUREFLEX ASSEMBLY

U.S. PATENT 5802710

Product of UNITED STATES

12US220001242 — Serial Number

Batch Manufacturing Date (two digit year and week) Manufacturing Plant Product Revision

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Product Specifications

COMMSCOPE®

F4RNA-PNRDF-1M5



Included Products

F4NR-HC — Type N Male Right Angle for 1/2 in FSJ4-50B cable