



F4RN-PNMMNF-M2

FSJ4RK-50B Jumper with interface types N Male and N Female, 0.25 m

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FSJ4-50B
Interface, Connector A	N Male
Interface, Connector B	N Female
Nominal Size	1/2 in
Length	0.250 m 0.820 ft
Specification Sheet Revision Level	A

Electrical Specifications

DTF, Connector A	-32.00 dB
DTF, Connector B	-32.00 dB

Jumper Assembly Sample Label



Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
China RoHS SJ/T 11364-2006
ISO 9001:2008

Classification

Compliant by Exemption
Above Maximum Concentration Value (MCV)
Designed, manufactured and/or distributed under this quality management system



Product Specifications

COMMSCOPE®

F4RN-PNMF-M2



Included Products

F4PNF-C — Type N Female for 1/2 in FSJ4-50B cable