



FSJ1RNA-PNMNM

**FSJ1RK-50B SureFlex® Jumper with interface types N Male and N Male, variable length**

## General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FSJ1-50B
Interface, Connector A	N Male
Interface, Connector B	N Male
Nominal Size	1/4 in
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 1-800-255-1479 (North America), 1-779-435-6500 (International), or an Andrew representative

## Electrical Specifications

DTF, Connector A	-28.00 dB
DTF, Connector B	-28.00 dB

## Jumper Assembly Sample Label



## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

# Product Specifications

COMMSCOPE®

FSJ1RNA-PNMM

