



FXL78-DMDF-21M

FXL-780 Jumper with interface types 7-16 DIN Male and 7-16 DIN Female, 21 M

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FXL-780
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Female
Nominal Size	7/8 in
Length	21.000 m 68.898 ft
Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached
Specification Sheet Revision Level	A

Electrical Specifications

DTF, Connector A	-34.00 dB
DTF, Connector B	-34.00 dB

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.07	30.00
1700–2200 MHz	1.1	26.40
2200–2500 MHz	1.1	26.40

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

Product Specifications

COMMSCOPE®

FXL78-D MDF-21M

RoHS 2011/65/EU
China RoHS SJ/T 11364-2006

Compliant by Exemption
Above Maximum Concentration Value (MCV)

