



FXL78-DMDM-22M  
FXL-780 Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 22 M

## General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FXL-780
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Male
Nominal Size	7/8 in
Length	22.000 m   72.178 ft
Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached
Specification Sheet Revision Level A	

## Electrical Specifications

DTF, Connector A	-34.00 dB
DTF, Connector B	-34.00 dB

## Jumper Assembly Sample Label



## Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.07	30.00
1700–2200 MHz	1.1	26.40
2200–2500 MHz	1.1	26.40

## Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

# Product Specifications

COMMScope®

FXL78-DMDM-22M

RoHS 2011/65/EU  
China RoHS SJ/T 11364-2006

Compliant by Exemption  
Above Maximum Concentration Value (MCV)

POWERED BY

