



FXL-DFDMMR-5M

FXL-540 Jumper with interface types 7-16 DIN Female and 7-16 DIN Male Right Angle, 5 m

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Cable Family	FXL-540
Interface, Connector A	7-16 DIN Female
Interface, Connector B	7-16 DIN Male
Nominal Size	1/2 in
Length	5.000 m 16.404 ft
Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached
Specification Sheet Revision Level	A

Electrical Specifications

DTF, Connector A	-34.00 dB
DTF, Connector B	-34.00 dB

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.07	29.00
1700–2200 MHz	1.1	26.40
2200–2500 MHz	1.13	24.00

Included Products

Product Specifications

COMMScope®

FXL-DFDMR-5M

POWERED BY



FXL-540 — FXL-540, HELIAX® Flexible Coaxial Cable, smoothwall aluminum, 1/2 in, black PE jacket

540EZDFV2 — 7-16 DIN Female EZfit® for 1/2 in FXL-540 cable