



FXL-DMDF-12M

FXL-540 Jumper with interface types 7-16 DIN Male and 7-16 DIN Female, 12 m

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	FXL-540
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Female
Nominal Size	1/2 in
Length	12.000 m 39.370 ft
Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached
Specification Sheet Revision Level	A

Electrical Specifications

DTF, Connector A	-34.00 dB
DTF, Connector B	-34.00 dB

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.05	32.00
1700–2200 MHz	1.09	27.30
2200–2500 MHz	1.10	26.40

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

FXL-D MDF-12M



ISO 9001:2008 Designed, manufactured and/or distributed under this quality management system

Included Products

540EZDM — 7-16 DIN Male EZfit® for 1/2 in FXL-540 cable

540EZDF — 7-16 DIN Female EZfit® for 1/2 in FXL-540 cable

FXL-540 — FXL-540, HELIAX® Flexible Coaxial Cable, smoothwall aluminum, 1/2 in, black PE jacket

540EZDMV2 — 7-16 DIN Male EZfit® for 1/2 in FXL-540 cable

540EZDFV2 — 7-16 DIN Female EZfit® for 1/2 in FXL-540 cable