



FXL-DMDM-1M5  
FXL-540 Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 1.5 m

## General Specifications

|                                    |                    |
|------------------------------------|--------------------|
| Body Style, Connector A            | Straight           |
| Body Style, Connector B            | Straight           |
| Cable Family                       | FXL-540            |
| Interface, Connector A             | 7-16 DIN Male      |
| Interface, Connector B             | 7-16 DIN Male      |
| Nominal Size                       | 1/2 in             |
| Length                             | 1.500 m   4.921 ft |
| Attachment, Connector A            | Factory attached   |
| Attachment, Connector B            | Factory attached   |
| Specification Sheet Revision Level | A                  |

## Electrical Specifications

|                  |           |
|------------------|-----------|
| DTF, Connector A | -34.00 dB |
| DTF, Connector B | -34.00 dB |

## Jumper Assembly Sample Label



## Return Loss/VSWR

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 698–960 MHz    | 1.05 | 32.00            |
| 1700–2200 MHz  | 1.09 | 27.30            |
| 2200–2500 MHz  | 1.10 | 26.40            |

## Regulatory Compliance/Certifications

| Agency | Classification |
|--------|----------------|
|--------|----------------|

FXL-DMDM-1M5

POWERED BY



ISO 9001:2008      Designed, manufactured and/or distributed under this quality management system

## Included Products

---

540EZDM — 7-16 DIN Male EZfit® for 1/2 in FXL-540 cable

FXL-540 — FXL-540, HELIAX® Flexible Coaxial Cable, smoothwall aluminum, 1/2 in, black PE jacket

540EZDMV2 — 7-16 DIN Male EZfit® for 1/2 in FXL-540 cable