



FXL-DMDMR-7M

FXL-540 Jumper with interface types 7-16 DIN Male and 7-16 DIN Male Right Angle, 7M

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Cable Family	FXL-540
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Male
Nominal Size	1/2 in
Length	7.000 m 22.966 ft
Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached
Specification Sheet Revision Level	A

Electrical Specifications

DTF, Connector A	-34.00 dB
DTF, Connector B	-34.00 dB

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698-960 MHz	1.07	29.00
1700-2200 MHz	1.10	26.40
2200-2500 MHz	1.14	24.00

Regulatory Compliance/Certifications

Product Specifications

COMMScope®

FXL-DMDMR-7M

POWERED BY



Agency

RoHS 2011/65/EU

China RoHS SJ/T 11364-2006

ISO 9001:2008

Classification

Compliant by Exemption

Above Maximum Concentration Value (MCV)

Designed, manufactured and/or distributed under this quality management system



Included Products

FXL-540 — FXL-540, HELIAX® Flexible Coaxial Cable, smoothwall aluminum, 1/2 in, black PE jacket

540EZDMV2 — 7-16 DIN Male EZfit® for 1/2 in FXL-540 cable