



FXL-NMNM-30

FXL-540 Jumper with interface types N Male and N Male, 30 ft

General Specifications

| | |
|------------------------------------|---------------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Cable Family | FXL-540 |
| Interface, Connector A | N Male |
| Interface, Connector B | N Male |
| Nominal Size | 1/2 in |
| Length | 9.144 m 30.000 ft |
| Attachment, Connector A | Factory attached |
| Attachment, Connector B | Factory attached |
| Specification Sheet Revision Level | A |

Electrical Specifications

| | |
|------------------|-----------|
| DTF, Connector A | -34.00 dB |
| DTF, Connector B | -34.00 dB |

Jumper Assembly Sample Label



Return Loss/VSWR

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 698–960 MHz | 1.05 | 32.00 |
| 1700–2200 MHz | 1.09 | 27.30 |
| 2200–2500 MHz | 1.10 | 26.40 |

Regulatory Compliance/Certifications

| Agency | Classification |
|--------|----------------|
|--------|----------------|

FXL-NMNM-30



ISO 9001:2008 Designed, manufactured and/or distributed under this quality management system

Included Products

540EZNM — Type N Male EZfit® for 1/2 in FXL-540 cable

FXL-540 — FXL-540, HELIAX® Flexible Coaxial Cable, smoothwall aluminum, 1/2 in, black PE jacket

540EZNMV2 — Type N Male EZfit® for 1/2 in FXL-540 cable