



L1A-PNMDM

LDF1-50 SureFlex® Jumper with interface types N Male and 7-16 DIN Male, variable length

General Specifications

| | |
|------------------------------------|--|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Cable Family | LDF1-50 |
| Interface, Connector A | N Male |
| Interface, Connector B | 7-16 DIN Male |
| Nominal Size | 1/4 in |
| Specification Sheet Revision Level | A |
| Variable Length | For custom lengths contact 1-800-255-1479 (North America), 1-779-435-6500 (International), or an Andrew representative |

Jumper Assembly Sample Label



Return Loss/VSWR

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 700-3000 MHz | 1.43 | 15.00 |

Regulatory Compliance/Certifications

| Agency | Classification |
|----------------------------|--|
| RoHS 2011/65/EU | Compliant by Exemption |
| China RoHS SJ/T 11364-2006 | Above Maximum Concentration Value (MCV) |
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |



L1A-PNMDM



Included Products

LDF1-50 — LDF1-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket

LDF1-50-43 — LDF1-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket