



L1B-PNMMNR

LDF1-50 SureFlex® Jumper with interface types N Male and N Male Right Angle, variable length

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Cable Family	LDF1-50
Interface, Connector A	N Male
Interface, Connector B	N Male
Nominal Size	1/4 in
Attachment, Connector B	Field attachment
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 1-800-255-1479 (North America), 1-779-435-6500 (International), or an Andrew representative

Electrical Specifications

DTF, Connector A	-28.00 dB
DTF, Connector B	-25.00 dB

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
70–850 MHz	1.13	24.00

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption

Product Specifications

COMMScope®

L1BPNMNR

POWERED BY



China RoHS SJ/T 11364-2006
ISO 9001:2008

Above Maximum Concentration Value (MCV)
Designed, manufactured and/or distributed under this quality management system



Included Products

LDF1-50 — LDF1-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket

L1TNR-PL — Type N Male Right Angle Positive Lock for 1/4 in LDF1-50 cable

LDF1-50-43 — LDF1-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket