

L2B-PNMMNR

LDF2-50 SureFlex® Jumper with interface types N Male and N Male Right Angle , variable length

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Cable Family	LDF2-50
Interface, Connector A	N Male
Interface, Connector B	N Male
Nominal Size	3/8 in
Attachment, Connector A	Factory attached
Attachment, Connector B	Field attachment
Orientation	90°
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 1-800-255-1479 (North America), 1-779-435-6500 (International), or an Andrew representative

Electrical Specifications

DTF, Connector A	-32.00 dB
------------------	-----------

Jumper Assembly Sample Label



Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Included Products

LDF2-50 — LDF2-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket

Product Specifications

COMMScope®

L2B-PNMMNR



L2TNR-PL — Type N Male Right Angle Positive Lock for 3/8 in LDF2-50 cable