



L2RNB-PNMTM

LDF2RK-50 SureFlex® Jumper with interface types N Male and TNC Male, variable length

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	LDF2-50
Interface, Connector A	N Male
Interface, Connector B	TNC Male
Nominal Size	3/8 in
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 1-800-255-1479 (North America), 1-779-435-6500 (International), or an Andrew representative

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.43	15.00

Regulatory Compliance/Certifications

Agency RoHS 2011/65/EU China RoHS SJ/T 11364-2006 ISO 9001:2008	Classification Compliant by Exemption Above Maximum Concentration Value (MCV) Designed, manufactured and/or distributed under this quality management system
---	--



L2RNB-PNMTM



Included Products

LDF2RK-50 — LDF2-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 3/8 in, black non-halogenated, fire retardant polyolefin jacket

L2TTM-PL — TNC Male Positive Lock for 3/8 in LDF2-50 cable