



## L4A-DM-12-P

**LDF4-50A SureFlex™ Jumper with interface type 7-16 DIN Male, 3.658 m**

### General Specifications

|                         |                     |
|-------------------------|---------------------|
| Body Style, Connector A | Straight            |
| Cable Family            | LDF4-50A            |
| Interface, Connector A  | 7-16 DIN Male       |
| Interface, Connector B  | Sold separately     |
| Length                  | 3.658 m   12.001 ft |

### Electrical Specifications

|                  |             |
|------------------|-------------|
| 3rd Order IMD    | -116.00 dBm |
| DTF, Connector A | -34.00 dB   |

### Jumper Assembly Sample Label



### Return Loss/VSWR

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 698–960 MHz    | 1.06 | 30.00            |
| 1700–2200 MHz  | 1.06 | 30.00            |

### Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |

### Included Products

LDF4-50A — LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

LDF4-50A-E1 — LDF4-50A-E1, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket