



## L4A-DMDM-20-PX

**LDF4-50A SureFlex™ Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 6.096 m**

### General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	LDF4-50A
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Male
Length	6.096 m   20.000 ft
Attachment, Connector B	Field attachment

### Electrical Specifications

3rd Order IMD	-100.00 dBm
DTF, Connector A	-32.00 dB

### Jumper Assembly Sample Label



### Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.10	26.40
1700–2200 MHz	1.10	26.40

### Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

### Included Products

LDF4-50A — LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

L4TDM-PSA — 7-16 DIN Male Positive Stop™ for 1/2 in AL4RPV-50, LDF4-50A cable

LDF4-50A-E1 — LDF4-50A-E1, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket