



L4A-DMDR-8-P
LDF4-50A SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male Right Angle, 2.438 m

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Cable Family	LDF4-50A
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Male
Nominal Size	1/2 in
Length	2.438 m 7.999 ft
Specification Sheet Revision Level B	

Electrical Specifications

3rd Order IMD	-116.00 dBm
DTF, Connector A	-34.00 dB
DTF, Connector B	-30.00 dB

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.08	28.00
1700–2200 MHz	1.08	28.00
2200–2700 MHz	1.13	24.00

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

L4A-DMDR-8-P

POWERED BY



ISO 9001:2008 Designed, manufactured and/or distributed under this quality management system

Included Products

LDF4-50A — LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket