



L4A-NMDM-25-P

LDF4-50A SureFlex® Jumper with interface types N Male and 7-16 DIN Male, 7.621 m

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	LDF4-50A
Interface, Connector A	N Male
Interface, Connector B	7-16 DIN Male
Nominal Size	1/2 in
Length	7.621 m 25.003 ft
Specification Sheet Revision Level	B

Electrical Specifications

3rd Order IMD	-112.00 dBm
DTF, Connector A	-34.00 dB
DTF, Connector B	-34.00 dB

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.10	26.40
1700–2200 MHz	1.10	26.40
2200–2700 MHz	1.13	24.00

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

L4A-NMDM-25-P

POWERED BY



Included Products

LDF4-50A — LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

LDF4-50A-E1 — LDF4-50A-E1, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket