

**L4A-PNMNM-10M****LDF4-50A SureFlex® Jumper with interface types N Male and N Male, 10 m**

General Specifications

| | |
|------------------------------------|----------------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Cable Family | LDF4-50A |
| Interface, Connector A | N Male |
| Interface, Connector B | N Male |
| Nominal Size | 1/2 in |
| Length | 10.000 m 32.808 ft |
| Specification Sheet Revision Level | A |

Electrical Specifications

| | |
|------------------|-----------|
| DTF, Connector A | -32.00 dB |
| DTF, Connector B | -32.00 dB |

Jumper Assembly Sample Label



Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
China RoHS SJ/T 11364-2006
ISO 9001:2008

Classification

Compliant by Exemption
Above Maximum Concentration Value (MCV)
Designed, manufactured and/or distributed under this quality management system



L4A-PNMMNM-10M

POWERED BY



Included Products

LDF4-50A — LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

LDF4-50A-E1 — LDF4-50A-E1, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket