

## L4A-XDMDF-2M

**LDF4-50A SureFlex™ Jumper with interface types 7-16 DIN Male and 7-16 DIN Female, 2 m**


### General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	LDF4-50A
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Female
Length	2.000 m   6.562 ft

### Electrical Specifications

3rd Order IMD	-116.00 dBm
---------------	-------------

### Jumper Assembly Sample Label



### Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
806-960 MHz	1.05	32.00
1700-2170 MHz	1.06	30.00

### Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

### Included Products

LDF4-50A — LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

LDF4-50A-E1 — LDF4-50A-E1, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket