



L4P43A-PDMDF-2M
LDF4-50A SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Female, 2 m

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	LDF4-50A
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Female
Nominal Size	1/2 in
Length	2.000 m 6.562 ft
Attachment, Connector B	Field attachment
Specification Sheet Revision Level	A

Electrical Specifications

DTF, Connector A	-32.00 dB
DTF, Connector B	-32.00 dB

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
800–970 MHz	1.15	23.13
1420–1530 MHz	1.15	23.13
1700–2180 MHz	1.15	23.13

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

Product Specifications

COMMScope®

L4P43A-PDMDF-2M

POWERED BY



RoHS 2011/65/EU

China RoHS SJ/T 11364-2006

ISO 9001:2008

Compliant by Exemption

Above Maximum Concentration Value (MCV)

Designed, manufactured and/or distributed under this quality management system



Included Products

LDF4-50A — LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

LDF4-50A-E1 — LDF4-50A-E1, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket