



## L4P43A-PDMDM-13M-X

**LDF4-50A SureFlex™ Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 13 m**

### General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	LDF4-50A
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Male
Length	13.000 m   42.651 ft
Attachment, Connector B	Field attachment

### Electrical Specifications

DTF, Connector A	-32.00 dB
------------------	-----------

### Jumper Assembly Sample Label



### Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
800–970 MHz	1.15	23.13
1420–1530 MHz	1.15	23.13
1700–2180 MHz	1.15	23.13

### Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

### Included Products

LDF4-50A — LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

L4TDM-PS — 7-16 DIN Male Positive Stop™ for 1/2 in LDF4-50A cable

L4TDM-PSA — 7-16 DIN Male Positive Stop™ for 1/2 in AL4RPV-50, LDF4-50A cable

LDF4-50A-E1 — LDF4-50A-E1, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket