



L4P43A-PDMNM-3M-X
LDF4-50A SureFlex® Jumper with interface types 7-16 DIN Male and N Male, 3 m

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	LDF4-50A
Interface, Connector A	7-16 DIN Male
Interface, Connector B	N Male
Nominal Size	1/2 in
Length	3.000 m 9.843 ft
Attachment, Connector B	Field attachment
Specification Sheet Revision Level	A

Electrical Specifications

DTF, Connector A	-32.00 dB
------------------	-----------

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
800–970 MHz	1.15	23.13
1420–1530 MHz	1.15	23.13
1700–2180 MHz	1.15	23.13

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

L4P43A-PDMNM-3M-X

POWERED BY



Included Products

LDF4-50A — LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

LDF4-50A-E1 — LDF4-50A-E1, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket