



L4-PDMDM-6

LDF4-50A Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 1.829 m

General Specifications

| | |
|------------------------------------|--------------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Cable Family | LDF4-50A |
| Interface, Connector A | 7-16 DIN Male |
| Interface, Connector B | 7-16 DIN Male |
| Nominal Size | 1/2 in |
| Length | 1.829 m 6.001 ft |
| Specification Sheet Revision Level | A |

Electrical Specifications

| | |
|------------------|-----------|
| DTF, Connector A | -32.00 dB |
| DTF, Connector B | -32.00 dB |

Jumper Assembly Sample Label



Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
China RoHS SJ/T 11364-2006
ISO 9001:2008

Classification

Compliant by Exemption
Above Maximum Concentration Value (MCV)
Designed, manufactured and/or distributed under this quality management system



L4-PDMDM-6

POWERED BY



Included Products

LDF4-50A — LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

L4TDM-PS — 7-16 DIN Male Positive Stop™ for 1/2 in LDF4-50A cable

L4TDM-PSA — 7-16 DIN Male Positive Stop™ for 1/2 in AL4RPV-50, LDF4-50A, HL4RPV-50 cable

LDF4-50A-E1 — LDF4-50A-E1, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket