

L4-PNMNR-1M-MAR

LDF4-50A Jumper with interface types N Male and N Male Right Angle, 1 m

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Cable Family	LDF4-50A
Interface, Connector A	N Male
Interface, Connector B	N Male
Length	1.000 m 3.281 ft

Electrical Specifications

DTF, Connector A	-32.00 dB
DTF, Connector B	-25.00 dB

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
4400–5000 MHz	1.14	24.00
7750–8500 MHz	1.14	24.00

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

LDF4-50A — LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

L4PNM-H — Type N Male for 1/2 in LDF4-50A cable


L4TNR-HC — Type N Male Right Angle for 1/2 in LDF4-50A cable

L4PNM — Type N Male for 1/2 in LDF4-50A cable

Product Specifications

COMMScope®

L4-PNMMNR-1M-MAR



LDF4-50A-E1 — LDF4-50A-E1, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket