



L4-UMNF-6

**LDF4-50A Jumper with interface types N Female and UHF Male, 1.829 m**

## General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	LDF4-50A
Interface, Connector A	N Female
Interface, Connector B	UHF Male
Nominal Size	1/2 in
Length	1.829 m   6.001 ft
Specification Sheet Revision Level	A

## Electrical Specifications

DTF, Connector A	-32.00 dB
DTF, Connector B	-10.00 dB

## Jumper Assembly Sample Label



## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU  
China RoHS SJ/T 11364-2006  
ISO 9001:2008

### Classification

Compliant by Exemption  
Above Maximum Concentration Value (MCV)  
Designed, manufactured and/or distributed under this quality management system



L4-UMNF-6



## Included Products

---

LDF4-50A — LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket

L4PNF — Type N Female for 1/2 in LDF4-50A cable

L44P — UHF Male for 1/2 in LDF4-50A cable

LDF4-50A-E1 — LDF4-50A-E1, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket