



245175

**Andrew 3M™ Cold Shrink™ Kit for 2-1/4 in to 1/4 in through 1/2 in connections**

## Dimensions

Nominal Size	1/2 in   1/4 in   2-1/4 in
Cable Diameter for Seal, maximum	35.56 mm   1.40 in
Cable Diameter for Seal, minimum	10.41 mm   0.41 in
Inner Diameter	80.77 mm   3.18 in
Length	381.00 mm   15.00 in
Width	83.31 mm   3.28 in

## General Specifications

Application	Provides additional moisture seal for cable connections
Applications per Kit	One 1/4 in–1/2 in to 2-1/4 in
Color	Black
Includes	One EPDM rubber tube   One sealing foam strip
Material Type	EPDM rubber
Package Quantity	1

## Mechanical Specifications

UV Resistance Test Method	UV condensation reference ASTM-G-53, light source UVA 340 fluorescent lamp
UV Resistance, minimum with no degradation	=1000 hours
Weather Resistance Test Method	04AS00-03.6.0   MIL-STD-1344A, Method 1002

## Packed Dimensions

Height	39.8 cm   15.7 in
Length	8.2 cm   3.2 in
Shipping Weight	0.38 kg   0.84 lb
Width	11.8 cm   4.6 in

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU  
China RoHS SJ/T 11364-2006  
ISO 9001:2008

**Classification**

Compliant  
Below Maximum Concentration Value (MCV)  
Designed, manufactured and/or distributed under this quality management system

