



250062

Messenger Wire Tie Wrap with spacer for RCT RADIAX® Radiating cable

- For added support, use with Andrew Stainless Steel Cable Ties (250058) at 5 meter intervals

Dimensions

Nominal Size	1-1/4 in 1-5/8 in 1/2 in 7/8 in
Compatible Diameter, maximum	114.000 mm 4.488 in
Height	25.40 mm 1.00 in
Length	406.00 mm 15.98 in
Width	12.70 mm 0.50 in

General Specifications

Hanger Type	Cable tie
Cables per Hanger	1
Color	Black
Material Type	Engineered plastic
Package Quantity	1

Mechanical Specifications

Flammability Test Method	UL 94-HB
Mounting	Messenger wire
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Pullout Force, maximum with no cable slippage	445 N 100 lbf
UV Resistance, minimum with no degradation	=100 hours exposure in accelerated UV life chamber

Packed Dimensions

Shipping Weight	0.02 kg 0.03 lb
-----------------	-------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system