

POWERED BY



243684-M

Angle Adapter, compact, M10 tapped hole

Dimensions

Inside Length	15.88 mm		0.63 in
Inside Width	15.88 mm		0.63 in
Outside Length	46.99 mm		1.85 in
Outside Width	38.10 mm		1.50 in

General Specifications

Adapter Type	Angle adapter
Material Type	Stainless steel
Package Quantity	10

Mechanical Specifications

Installation Torque, maximum	13.0 ft lb
Installation Torque, minimum	11.0 ft lb
Material Thickness	2.972 mm 0.117 in
Maximum Loading	Double stack, 1-5/8 in cable
Mounting	M10 tapped hole

Packed Dimensions

Height	14.0 cm		5.5 in
Length	11.0 cm		4.3 in
Shipping Weight	1.59 kg		3.50 lb
Width	14.0 cm		5.5 in

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
China RoHS SJ/T 11364-2006
ISO 9001:2008

Classification

Compliant
Below Maximum Concentration Value (MCV)
Designed, manufactured and/or distributed under this quality management system

