

**42615-10****Butyl Rubber Tape, 24 in**

## Dimensions

Nominal Size	1-1/4 in   1-5/8 in   1/2 in   1/4 in   2-1/4 in   3/8 in   5/8 in   7/8 in
Length	609.60 mm   24.00 in
Width	63.50 mm   2.50 in

## General Specifications

Application	Provides additional moisture seal for cable connections
Applications per Kit	One 1/2 in–2-1/4 in   One 1/2 in–7/8 in   One 1/2 in–7/8 in to device   Two 1/2 in–1/2 in
Color	Black
Material Type	Butyl rubber tape
Package Quantity	1

## Mechanical Specifications

UV Resistance Test Method	Butyl test method in QUV weatherometer cycle of 8 hours UV at 150 °F then 4 hours of condensation at 104 °F
UV Resistance, minimum with no degradation	=1000 hours
Weather Resistance Test Method	04AS00-03.6.0   MIL-STD-1344A, Method 1002

## Packed Dimensions

Height	6.4 cm   2.5 in
Length	2.5 cm   1.0 in
Shipping Weight	0.17 kg   0.37 lb
Width	69.9 mm   2.8 in

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
China RoHS SJ/T 11364-2006	Below Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

