



C61B01P36 | C61B01P3601
Power Cable for Receive Multicouplers and Low Loss Combiners, 8 m

General Specifications

Product Type	Power cable
Application	Low loss combiner Receive multicoupler

Mechanical Specifications

Conductor Type	24 AWG
Conductors, quantity	3
Connector Interface	Pluggable terminal block
Material Type	PVC

Dimensions

Length	8.0 m 26.2 ft
Weight	210.0 g 0.5 lb

Product Specifications

COMMScope®

C61B01P36 | C61B01P3601

POWERED BY



Outline Drawing

