



CO-100

Crossover Plate, joins 1-1/2 in to 3-1/2 in OD round members

Dimensions

Mounting Diameter, maximum	88.9 mm		3 1/2 in
Mounting Diameter, minimum	38.1 mm		1 1/2 in
Height	203.2 mm		8.0 in
Length	254.0 mm		10.0 in
Weight	7.3 kg		16.0 lb
Width	152.4 mm		6.0 in

General Specifications

Product Type	Clamp set
Tower Taper	Non-tapered
Includes	Clamps Plates
Material Type	Hot dip galvanized steel
Mounting	Crossover plate
Package Quantity	1

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system