



CO-400
Crossover Plate, joins 2 in to 5 in OD to 4 in to 9 in OD round member

Dimensions

Mounting Diameter, maximum	127.0 mm		5 in
Mounting Diameter, minimum	50.8 mm		2 in
Height	304.8 mm		12.0 in
Length	203.2 mm		8.0 in
Mounting Diameter 2, maximum	228.6 mm		9 in
Mounting Diameter 2, minimum	101.6 mm		4 in
Weight	13.6 kg		30.0 lb
Width	304.8 mm		12.0 in

General Specifications

Product Type	Clamp set
Tower Taper	Non-tapered
Includes	Clamps Plates
Material Type	Hot dip galvanized steel
Mounting	Crossover plate
Package Quantity	1

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system