



MT-374  
Stainless Steel Threaded Rod, 3/8 in x 36 in

## Dimensions

Pipe Outer Diameter	9.5 mm   3/8 in
Height	25.4 mm   1.0 in
Length	914.4 mm   36.0 in
Weight	0.7 kg   1.5 lb
Width	25.4 mm   1.0 in

## General Specifications

Product Type	Threaded rods and couplers
Material Type	Stainless steel
Includes	Threaded rod
Material Thickness	9.5 mm   3/8 in
Package Quantity	1

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system