



MT-378
Galvanized Threaded Rod, 3/8 in x 120 in

Dimensions

Pipe Outer Diameter	9.5 mm		3/8 in
Height	25.4 mm		1.0 in
Length	3.0 m		10.0 ft
Weight	2.3 kg		5.0 lb
Width	25.4 mm		1.0 in

General Specifications

Product Type	Threaded rods and couplers
Material Type	Hot dip galvanized steel
Includes	Threaded rod
Material Thickness	9.5 mm 3/8 in
Package Quantity	1

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system